

Main function

- Advanced luminous technology, no glare, no stroboscopic, light softly
- High technology light conductor, long life, and minimal droop
- Touch the switch, the brightness is adjustable, operation more convenient
- 3 color temperature adjustment, feels more comfortable
- Three-dimensional all-round illumination angle satisfies the requirement of different using environment.
- Foldable construture, small volume
- With calendar display & alarm clock & thermometer functions

Saving
1/3

than traditional bulb

“0”
UV light

No hurt the skin

Eye protection
soft light

Dizzy-proof light filter

Nature

Natural light

Adjustable

Color temperature adjustment


Eco-friendly

Free mercury & Lead


Specification

Material	ABS+Metal	Input	DC5V/1A
Maximum current	5V 800mA		
Warm white light CTT:2800-3300K /Cold white light CTT:6000-6500K/ Natural light CTT :3800-4400K LED lifetime:40000Hours LED quantity:4pcs SMD 5050 warm white LEDs +10pcs SMD 5050 cold white LEDs			
LCD display with calendar/alarm clock/thermometer functions			
Emitting way	Direct emitting	Power consumption	4W
Intensity of illumination	800LUX	CRI	> 70
Working temperature	<50°	Power factor	>0.4
Switch mode	Touch		
Product N.W.	690g		
Product size	L145*W145*H330mm		


Operation instruction



- Connect the power adapter in the rear of the lamp holder




- Press the power key can open the light(ref the details from operation instruction)




Lamp head the range of activities:

- Please hold the lamp holder at the same time when adjust the Angle of light head .
- Lamp head adjustable range of 180° (excessive adjustment activity joint part of the product can lead to functional damage) .




Lamp arm the range of activities:

- Lamp arm forward range: 90°
- Please hold the lamp holder at the same time when adjust the Angle of lamp arm .




Operation guidance

- Touch switch: Brightness adjustment



- Open the lamp: press Power key to open or close the lamp directly
- Brightness adjustment: Press Power key when plug in, click strengthen key can increase the lamp brightness, click weaken key can decrease the lamp brightness
- Light mode: Press M key to adjust the color temperature, 3 modes
 - 1: Warm white light
 - 2: Cold white light
 - 3: Natural light

- Calendar display operation:



- Date & Time setting:

1. Under normal mode, press “Set” key enter date and time setting mode, press “Set” again enter the next setting. The sequence of setting as below: hour-minute-year-month-day-back.
2. Press “Up” and “Down” setting, the day of week will vary accordingly.
3. Under setting mode, press “Mode” key or no operation in 60 seconds will back from set mode, and display the time
4. Under normal mode, Press “Up” transfer 12 and 24 hours format.

- Snooze function:

1. Under normal mode, press “Mode” enter alarm mode
2. Under alarm mode, press “Set” enter alarm setting, press “Set” again enter the next setting, the sequence of setting as below: hour-minute-snooze-music-back
3. Press “Up” and “Down” key to set
4. Under alarm mode, press “Up” and “Down” can open and close the function of alarm & snooze function, press it again enter the next function, the sequence as below : open the alarm-open the snooze -close alarm and snooze
5. When reach the alarm time, the alarm will last 1 minute, snooze time reach, alarm will ring again, press “Set” key or any button can stop the alarm

- Temperature transfer
Under normal mode, press “Down” key transfer Celsius and Fahrenheit