

## Warranty Card

**Applicable for:**

- Since buying date, the user enjoys one year free repair services under normal use. After one year, will be charged according to each component part cost.
- In case change component part, will be charged according to our company's component part cost list.
- The following situations not free repair in Warranty period.
  - 1) Damage caused by natural earthquake, rat disaster, and unnormal use.
  - 2) Damage caused in transportation, fall, and unproper storage.
  - 3) Consumable component, such as spare parts, batteries, light bulbs, etc.
  - 4) Warranty information record is not complete, no purchase date, no buying shop seal, etc.
  - 5) Featured using environment, such as humidity, sulfur area, high salty and the ship, etc, easy corrosion area.
  - 6) Using not according to the instructions.
  - 7) Special offer.
- When return to factory for repair, the user should make sure the LED lamp packed properly, to avoid any damage during transportation.
- Factory not responsible for the damages caused by the user themself unproper disassemble.


Important!  
Thank you for purchasing our products.  
To guarantee your rights, please fill in this form properly, thank you!

Name	
Address	
Telephone	
Invoice number	
Purchase date	
Item number	
dealers	⚠ Note: this field requires the dealers seal!

⚠ Warning: please keep this warranty paper for repair presentation.

Attention:

- Do not Self-disassemble the product, to avoid any electric shock.
- Please use vender's specified adapter and power socket, to maintain normal working.
- Please do not over-adjusting the joint activity parts, to avoid any damage to the lamp.
- Please do not use the lamp in high-temperature or high-humidity environment.
- Please don't look at the LED lightsouce straightly, to avoid your eyes hurt.
- In case below conditions occur, please pull out the power cord, stop using (if needed, please call for help) :
  - The power cord or power plug break
  - The lamp holder damp or rain
  - The shell and joint activities of the lamp holder breaks
  - The lamp holder smokes or sparks
  - The abnormal flickering or break of the LED light bulb



Main function

- Advanced luminous technology, no glare, no stroboscopic,light softly.
- High technology light conductor, long life, and minimal droop.
- Touch the switch, the brightness is adjustable, operation more convenient.
- 3 colors temperature adjustment,more comfortable.
- Three-dimensional all-round illumination angle satisfies the requirement of different using environment.
- Foldable constructure,small volume.
- Aluminum fin ensures the LED long life time.

Saving  
1/3  
than traditional bulb

"0"  
UV light  
No hurt the skin

Eye  
protection  
soft light  
Dizzy-proof light filter

Nature  
Natural light


Color  
temperature  
tunable  
Color temperature Mercury &Lead tunable

Eco-  
friendly  
Free


Specification

Shell material	ABS+Metal	Power supply	DC5V, 1A
Working current	800mA		
Color temperature adjustment: Cold light: 5500-6000K, Warm light: 2800-3300K, Natural light: 4000-4500K Per LED:20LM, LED life time:35000hours			
LEDs quantity: 14pcs SMD 5050 LEDs( 10pcs cold light LEDs+4pcs warm light LEDs)			
Light way	Vertical light	Power consumption	4W
Max luminous	800LUX	CRI	>80
Working temperature	<50°	Power factor	>0.8
Switch way	Touch switch		
Product N.W	710g		
Product size	H550mm*L150.5mm*W150.5mm		


User guidance



■ Insert the USB cable into DC interface behind product.




■ Touch the button to light on (please refer to operation instructions for details)



The range of lamp head activities :  
■ When adjusting the lamp head, please hold the base  
■ Lamp head adjusting range:180° (excessive adjustment may cause damage)

Installing instructions



Adjustable angle of the Lamp arm :  
■ Adjustable angle of the Lamp arm:90°  
■ When adjusting the lamp arm, please hold the base.

Operating instruction

■ Touch switch : Light adjustment (As shown)

M	⏻	+	-
Mode	Power	highlight	reduce brightness

- Light on Lamp: Touch ON/OFF switch
- Brightness adjustment: Plug in lamp when press the power switch, then brightest;Press highlight or reduced brightness switches(+ and - 5 strengths each 20%), increase or decrease the brightness of the lamp.
- Light mode : Press M key to adjust color temperature, 3 modes :
  1. Cold light
  2. Warm light
  3. Natural light

红色实线为刀模 ( 刀模不印刷出来)  
红色虚线为折线 ( 虚线不印刷出来 )